


5/16/55
Sales Tax

\$20.00
.20

INSTRUCTIONS FOR ASSEMBLY OF
PEDESTAL TYPE
TOOL STAND 99-2224



FOR THICKNESS PLANER - CAT. NO. 2370



SEARS, ROEBUCK and CO.

LITHOGRAPHED IN U. S. A.

SOURCE FORM 45859



Through the use of Casters, which may be purchased under Cat. No. 2819, you can better utilize your Workshop Area.

RECOMMENDED
HEIGHT 36"

CLAMP

MOTOR
MOUNT
BRACKET

MOTOR MOUNT BASE

BRACKET

BASE

ASSEMBLY INSTRUCTIONS

Assemble the column into the base casting and tighten the square head set screw securely. Attach your motor to the motor mount base with four 5/16-18 x 2" square head bolts, and the nuts and washers provided. Position the motor mount bracket and clamp, as shown in illustration, and slide entire unit over column to an approximate position. Secure lightly for final adjustment.

Position large bracket on column and tighten set screw.

Fasten your thickness planer to the assembled tool stand using the remaining four bolts, nuts and washers.

Final adjustments can now be made for belt installation.

1. Shift motor on motor base until the two pulleys are in the same plane.
2. Adjust entire motor mount assembly up or down on column for proper tensioning of belt.






A bracket is supplied which will permit mounting the POWR PANL, Cat. No. 2120 on the tool. This is an "L" shaped bracket. One side is wider than the other which will allow various means of mounting the POWR PANL to the tool. Mount the switch to best suit your needs. The illustration showing the mounting position is a suggested method only.

AVAILABLE ACCESSORIES

PURCHASE FROM YOUR NEAREST SEARS RETAIL STORE OR MAIL ORDER HOUSE.

FOR READY MOBILITY USE SET OF 4 CASTERS — CAT. NO. 2819

FOR SAFE HOOK-UP USE POWR PANL — CAT. NO. 2120



**PURCHASE THESE TOOL STANDS
FROM YOUR NEAREST SEARS
RETAIL STORE OR MAIL ORDER
HOUSE.**

